

contacta RX30

Rechargeable Hearing Loop Listener



CONTACTA LARGE AREA LOOP SYSTEMS

The Contacta RX30 Rechargeable Hearing Loop Listener is a compact listening device for use with hearing loop systems. It enables people to listen to a hearing loop system as if they were wearing a hearing device switched to the T-Coil Program.

Physical Data

Dimensions	Height – 4.40" Width – 2.75" Depth – 0.86"
Weight	1.21lbs
Construction	ABS Plastic
Finish	Black

Technical Data

Audio Frequency Transmission Range	85Hz - 6kHz +/- 0.5dB
Low Cut	400Hz - 6kHz - 3dB
Distortion	<0.5% THD @ 1KHz
Signal to Noise Ratio	Typ. 60 dB
Output Power	>100mW @16Ω
Battery Life	50 hours minimum
Battery Type	x2 Rechargeable AAA NiMh batteries
Charge Time (full capacity)	6 hours (approximated)



RX30

RX30, x2 rechargeable batteries, lanyard and belt clip

RX30-HS

RX30, x2 rechargeable batteries, lanyard, belt clip and a pair of headphones

RX30-EB

RX30, x2 rechargeable batteries, lanyard, belt clip and 6 pairs of earbuds

Applications

- › For users with hearing loss but do not have a personal hearing device or when a user does not have a t-coil feature in their hearing device.
- › To test if a hearing loop system is functioning.

Features

- › Flat frequency response
- › Brass cut filter

Components

- › RX30 Hearing Loop Listener
- › x2 Rechargeable batteries
- › Lanyard
- › Belt clip

Accessories

- › RX30-DC5 - 5 Bay Charger
- › BATT-RX30 - Replacement Batteries

Standards

- › FCC class "B" emissions
- › ICES-003

contacta

Phone: (616) 392-3400
Email: sales@contactainc.com
www.contactainc.com